

## Product data sheet

### Characteristics

# 752IR2RC

PIR Sensor, 360deg, 15m, Dual Channel,  
Remote Control Option



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Fluorescent tube: 900 VA Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V
Colour tint	White

### Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...2000 lux
Horizontal detection angle	360 °
Detection range	Radius: 14000 mm
Device mounting	Surface Flush
Mounting height	2.5 m

### Environment

IP degree of protection	IP52 IP40
-------------------------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.6 cm
Package 1 Width	12.1 cm
Package 1 Length	17.8 cm
Package 1 Weight	433.1 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins