

## Product data sheet

### Characteristics

# 752IR2RC

ARGUS Movement detectors, PIR Sensor,  
360deg, 15m, Dual Channel, Remote Control  
Option



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Fluorescent tube: 900 VA Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V
Colour tint	White

### Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Number output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...2000 lux
Horizontal detection angle	360 °
Detection range	Radius: 14000 mm
Device mounting	Surface Flush
Mounting height	2.5 m






### Environment

IP degree of protection	IP52 IP40
-------------------------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.6 cm
Package 1 Width	12.1 cm
Package 1 Length	17.8 cm
Package 1 Weight	433.1 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins