

## Product data sheet

### Characteristics

# 753CF1

Motion Sensor Infrascan - Passive infrared -  
Indoor - 3.5m detection radius - One-channel -  
240 V



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	Halogen lamp: 1000 W, AC Incandescent lamp: 1000 W, AC Compact fluorescent lamp: 3 x 23 W, AC Fluorescent lamp: 200 VA, AC
Colour tint	White

### Complementary

[Ue] rated operational voltage	220...240 V
Network frequency	50/60 Hz
[Ue] rated operational voltage	220...240 V
Output current	10 A
Number of channels	1
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0.035 m
Detection range	Radius
Material	ABS + PC matt
Device mounting	Ceiling
Mounting height	2.5 m

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>