

Product data sheet

Characteristics

753CF2

Motion Sensor Infrascan - Passive infrared -
Indoor - Two-channel - 3.5m detection radius -
240 V



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V Incandescent lamps: : 1000 W - 230 V Halogen lamp: : 900 W - 230 V Halogen lamp with standard electronic transformer: 250 VA Halogen lamp with standard ferromagnetic transformer: 500 VA Capacitive: : 6 A, 21 µF Capacitive: : 10 A, 14 µF Fluorescent tube: 200 VA
Colour tint	White




Complementary

Network frequency	50/60 Hz
Input function	Switch
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0.035 m
Detection range	Radius: 3500 mm
Mounting height	2.5 m

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
