

## Product data sheet

### Characteristics

# 753CF2

PIR Sensor 360 Degree Flush Mount, Dual Load Output, 240VAC 50HZ



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V Incandescent lamps: : 1000 W - 230 V Halogen lamp: : 900 W - 230 V Halogen lamp with standard electronic transformer: 250 VA Halogen lamp with standard ferromagnetic transformer: 500 VA Capacitive: : 6 A, 21 µF Capacitive: : 10 A, 14 µF Fluorescent tube: 200 VA
Colour tint	White

### Complementary

Network frequency	50/60 Hz
Input function	Switch
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0.035 m
Detection range	Radius: 3500 mm
Mounting height	2.5 m

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	12.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	400.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins