

## Product data sheet

### Characteristics

# 753R-WE

Motion Sensor Infrascan - Passive infrared -  
Indoor - 5m detection radius - 3-wire - 240 V -  
10 A - White Electric



### Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Device application	Lighting
Sensor type	PIR
Product specific application	Staircase monitoring
Colour	White electric

### Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Inrush current	10 A
Power range	<= 230 W
Protection type	Creep zone protection
Function available	Automatic with manual override
Movement detection area	14 m
Horizontal detection angle	0...360 °
Time delay range	0...5 s (switch-on)
Duty cycle	20 min
Detection face	Lateral: 7 m Frontal: 7 m
Material	Plastic
Surface finish	Brilliant
Device mounting	Flush
Mounting support	Ceiling
Mounting height	2.4 m
Colour code	WE

### Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...50 °C
Environmental health and issues	Halogen free

### Packing Units

Package 1 Weight	204.000 g
Package 1 Height	165.000 mm
Package 1 width	85.000 mm
Package 1 Length	125.000 mm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	<a href="#">End Of Life Information</a>