

Product data sheet

Characteristics

753R-WE

Clipsal - Motion Sensor, Motion Infrared Sensor, 10A, 3 Wire, Flush Mount



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Device application	Lighting
Sensor type	PIR
Product specific application	Staircase monitoring
Colour	White electric

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Inrush current	10 A
Power range	<= 2300 W
Protection type	Creep zone protection
Function available	Automatic with manual override
Movement detection area	14 m
Horizontal detection angle	0...360 °
Time delay range	0...5 s (switch-on)
Duty cycle	20 min
Detection face	Lateral: 7 m Frontal: 7 m
Material	Plastic
Surface finish	Brilliant
Device mounting	Flush
Mounting support	Ceiling
Mounting height	2.4 m
Colour code	WE

Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	204 g

Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3354.8 g
Unit Type of Package 3	PAL
Number of Units in Package 3	160
Package 3 Height	120 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	63676.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information