

## Product data sheet

### Characteristics

# 7G80/D10/U

## SWITCH CAM ON/OFF 3P 80A



### Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

### Complementary

Switch function	2-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	2
Connector type	Screw terminals
[Ui] rated insulation voltage	660 V AC
[Ith] conventional free air thermal current	80 A
Number of poles	3
Rated operational power in W	37 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	80 A

### Packing Units

Package 1 Weight	0.680 kg
------------------	----------