

Product data sheet

Characteristics

7GF10/53/U

SWITCH CAM C/OVER 3P 10A



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	9 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	10 A
Number of poles	3
Rated operational power in W	3 kW
Switching angle	60 °
Fuse type	3 KA, gG 3 kA, gL
Maximum short-circuit current	10 A

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Package 1 Weight	84.000 g
Package 1 Height	55.000 mm
Package 1 width	120.000 mm
Package 1 Length	55.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------