

Product data sheet

Characteristics

7GF10/54/U

7 Series Cam Switches, 1 Pole, Changeover Switch Without Off Marked 1-2



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	2-way
Mounting holes diameter	9 mm
[Us] rated supply voltage	415 V DC
Number of contacts	2
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	10 A
Number of poles	1
Rated operational power in W	3 kW
Switching angle	90 °
Fuse type	3 KA, gG 3 kA, gL
Maximum short-circuit current	10 A

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------