

Product data sheet

Characteristics

7GF10/D51/U

Changeover Switch, 7 Series Cam Switches, 1 Pole, Marked Man / Off / Auto

Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	9 mm
[Us] rated supply voltage	415 V AC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	10 A
Number of poles	1
Rated operational power in W	3 kW
Switching angle	60 °
Fuse type	3 KA, gG 3 kA, gL
Maximum short-circuit current	10 A

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	5.4 cm
Package 1 Length	11.4 cm
Package 1 Weight	0.061 kg

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations