

## Product data sheet

### Characteristics

# 7GF20/52/U

## SWITCH CAM C/OVER 2P 20A



### Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

### Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	20 A
Number of poles	2

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	115 g
Package 1 Height	52 mm
Package 1 width	52 mm
Package 1 Length	112 mm

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------