

## Product data sheet

### Characteristics

# 7GF20/D11/U

## SWITCH FOR/OFF/REV 3P 20A



### Main

Product brand	Clipsal
Range of product	Series 7

### Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	20 A
Number of poles	3
Rated operational power in W	7.5 kW
Switching angle	60 °
Fuse type	5 KA, gG 5 kA, gL
Maximum short-circuit current	20 A

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Package 1 Weight	0.12 kg
------------------	---------

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------