

Product data sheet

Characteristics

7GF20/D51/U

7 Series Cam Switches, 1 Pole, Changeover
Switch Marked Man / Off / Auto



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V AC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	20 A
Number of poles	1
Rated operational power in W	7.5 kW
Switching angle	60 °
Fuse type	5 KA, gG 5 kA, gL
Maximum short-circuit current	20 A

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	11.3 cm
Package 1 Weight	94.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	11.7 cm
Package 2 Width	25.0 cm
Package 2 Length	31.0 cm
Package 2 Weight	1880.0 g

