

## Product data sheet

### Characteristics

# 7GN12/52/U

## 7 Series Cam Switches, 2 Pole, 12A, Changeover Switch with Off Marked 1-O-2



### Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

### Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	12 A
Number of poles	2
Rated operational power in W	6 kW
Switching angle	60 °
Fuse type	3 KA, gG 3 kA, gL
Maximum short-circuit current	16 A

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------