

Product data sheet

Characteristics

7GN12/D51/U

SWITCH CAM MAN/O/AUTO 12A



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	12 A
Number of poles	1
Rated operational power in W	6 kW
Switching angle	60 °
Fuse type	3 KA, gG 3 kA, gL
Maximum short-circuit current	16 A

Packing Units

Package 1 Weight	0.080 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------