

Product data sheet

Characteristics

7GN125/10/U

SWITCH CAM 0-1 3P 10A



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	2-way
Mounting holes diameter	16 mm
[Us] rated supply voltage	415 V AC
Number of contacts	2
Connector type	Screw terminals
[I _{th}] conventional free air thermal current	125 A
Number of poles	3
Rated operational power in W	45 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	125 A

Packing Units

Package 1 Weight	1.000 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.