

Product data sheet

Characteristics

7GN25/53/U

SWITCH CAM 3P 25A CH/OVER



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[I _{th}] conventional free air thermal current	25 A
Number of poles	3
Rated operational power in W	11 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	25 A

Packing Units

Package 1 Weight	157.000 g
Package 1 Height	53.000 mm
Package 1 width	53.000 mm
Package 1 Length	113.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------