

## Product data sheet

### Characteristics

# 7GN25/D52/U

## SWITCH CAM 2P 25A CH/OVER



### Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

### Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[I <sub>th</sub> ] conventional free air thermal current	25 A
Number of poles	2
Rated operational power in W	11 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	25 A

### Packing Units

Package 1 Weight	1.000 kg
------------------	----------

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------