

## Product data sheet

### Characteristics

# 7GN32/53/U

## SWITCH CAM 3P 32A CH/OVER



### Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

### Complementary

Switch function	3-way
Mounting holes diameter	14 mm
[Us] rated supply voltage	415 V AC
Number of contacts	3
Connector type	Screw terminals
[I <sub>th</sub> ] conventional free air thermal current	32 A
Number of poles	3
Rated operational power in W	15 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	40 A

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	287.0 g
Package 1 Height	7.4 cm
Package 1 width	7.6 cm
Package 1 Length	14.5 cm

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------