

Product data sheet

Characteristics

7GN32/D10/U

SWITCH CAM OFF/ON 3P 32A



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	2-way
Mounting holes diameter	14 mm
[Us] rated supply voltage	415 V DC
Number of contacts	2
Connector type	Screw terminals
[I _{th}] conventional free air thermal current	32 A
Number of poles	3

Packing Units

Package 1 Weight	0.243 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.