

Product data sheet

Characteristics

7GN32/D11/U

Reversing Switch, 7 Series Cam Switches, 3 Pole, Marked Fwd / Off / Rev

Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor


Complementary

Switch function	3-way
Mounting holes diameter	14 mm
[Us] rated supply voltage	415 V AC
Number of contacts	3
Connector type	Screw terminals
[Ith] conventional free air thermal current	32 A
Number of poles	3
Rated operational power in W	15 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	40 A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	276.0 g

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.