

Product data sheet

Characteristics

7GN32/D53/U

SWITCH CAM 3P 32A CH/OVER



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	14 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[I _{th}] conventional free air thermal current	32 A
Number of poles	3
Rated operational power in W	15 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	40 A

Packing Units

Package 1 Weight	289.000 g
Package 1 Height	71.000 mm
Package 1 width	71.000 mm
Package 1 Length	143.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------