

Product data sheet

Characteristics

7GN63/52/U

63A CAM SWITCH



Main

| | |
|-------------------------|----------------------|
| Product brand | Clipsal |
| Range of product | Series 7 |
| Electrical circuit type | Changeover contactor |

Complementary

| | |
|--|------------------------|
| Switch function | 3-way |
| Mounting holes diameter | 14 mm |
| [Us] rated supply voltage | 415 V DC |
| Number of contacts | 3 |
| Connector type | Screw terminals |
| [I _{th}] conventional free air thermal current | 63 A |
| Number of poles | 2 |
| Rated operational power in W | 15 kW |
| Switching angle | 60 ° |
| Fuse type | 10 KA, gG 10 kA, gL |
| Maximum short-circuit current | 63 A |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.2 cm |
| Package 1 Width | 7.2 cm |
| Package 1 Length | 14.5 cm |
| Package 1 Weight | 303 g |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|