

Product data sheet

Characteristics

7GN63/D53/U

Series 7 Rotary Cam Switch, 3 Pole,
Changeover Switch Marked Man / Off / Auto



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	14 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ith] conventional free air thermal current	63 A
Number of poles	3
Rated operational power in W	30 kW
Switching angle	60 °
Fuse type	10 KA, gG 10 kA, gL
Maximum short-circuit current	63 A

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7.4 cm
Package 1 Length	14.8 cm
Package 1 Weight	380 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------