

## Product data sheet

### Characteristics

# 9016TCM-GY

## conduit corrugated turbo pvc medium duty

### 16mm / 50m



#### Main

Colour	Grey
Product brand	Clipsal

#### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 10.3 mm
External diameter	16 mm




#### Environment

Environmental characteristic	RoHS compliant conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

#### Packing Units

Package 1 Weight	8.120 kg
Package 1 Height	198.000 mm
Package 1 width	280.000 mm
Package 1 Length	292.000 mm

#### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>