

Product data sheet

Characteristics

9020CHF-BK

Corrugated Conduit, 20mm x 10m



Main

| | |
|---------------|---------|
| Colour | Black |
| Product brand | Clipsal |

Complementary

| | |
|-------------------|----------|
| Colour code | BK |
| Material | PC |
| Stub stiffness | Flexible |
| External diameter | 20 mm |

Environment

| | |
|---------------------------------------|-----------------|
| Environmental characteristic | Flame retardant |
| Ambient air temperature for operation | -45...150 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | Db |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.0 cm |
| Package 1 Width | 38.0 cm |
| Package 1 Length | 38.0 cm |
| Package 1 Weight | 509.0 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |