

## Product data sheet

### Characteristics

# 9020CMS-GY

## Clipsal - Cable Management, Corrugated Conduit, Medium Duty Sheathed, PVC, 20mmx50m



### Main

Colour	Grey
Product brand	Clipsal

### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Inner: 14.1 mm
External diameter	20 mm

### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.8 cm
Package 1 Width	42.0 cm
Package 1 Length	46.5 cm
Package 1 Weight	6.42 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>