

Product data sheet

Characteristics

9020TCM-GY

conduit corrugated turbo pvc medium duty

20mm / 50m



Main

Colour	Grey
Product brand	Clipsal

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 13.9 mm
External diameter	20 mm

Environment

Environmental characteristic	Conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

Packing Units

Package 1 Weight	3.780 kg
Package 1 Height	210.000 mm
Package 1 width	470.000 mm
Package 1 Length	470.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile