

## Product data sheet

### Characteristics

# 9025CHD10-EO

## conduit corrugated pvc heavy duty 25mm / 10m



### Main

Colour	Electric orange
--------	-----------------

### Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 17.6 mm
External diameter	25 mm

### Environment

Environmental characteristic	RoHS compliant conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

### Packing Units

Package 1 Weight	1400.000 g
Package 1 Height	100.000 mm
Package 1 width	370.000 mm
Package 1 Length	370.000 mm

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.