

Product data sheet

Characteristics

9025CMS10-GY

CONDUIT COR M/D SHEATHED 25MM/10M



Main

| | |
|---------------|---------|
| Colour | Grey |
| Product brand | Clipsal |

Complementary

| | |
|-------------------|--------------------------|
| Colour code | GY |
| Material | PVC (polyvinyl chloride) |
| Stub stiffness | Flexible |
| Mounting support | Concrete |
| Diameter | Inner: 18.3 mm |
| External diameter | 25 mm |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -15...65 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 1.740 kg |
|------------------|----------|

Offer Sustainability

| | |
|-------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
|-------------------|--|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.