

## Product data sheet

### Characteristics

# 9025CMS20-GY

## Clipsal - Cable Management, Corrugated Conduit, Medium Duty Sheathed, 25mm x 20m



### Main

Colour	Grey
Product brand	Clipsal

### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Mounting support	Concrete
Diameter	Inner: 18.3 mm
External diameter	25 mm


### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.8 cm
Package 1 Width	37.4 cm
Package 1 Length	37.4 cm
Package 1 Weight	3.4 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

