

# Product data sheet

## Characteristics

# 9025CMS20-GY

## CONDUIT COR M/D SHEATHED 25MM/20M



### Main

Colour	Grey
Product brand	Clipsal

### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Mounting support	Concrete
Diameter	Inner: 18.3 mm
External diameter	25 mm

### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Package 1 Weight	3.400 kg
Package 1 Height	98.000 mm
Package 1 width	374.000 mm
Package 1 Length	374.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>