

Product data sheet

Characteristics

9025TCM-GY

Clipsal - Cable Management, Corrugated Conduit, Turbo, Medium Duty, 25mm x 50m



Main

| | |
|---------------|---------|
| Colour | Grey |
| Product brand | Clipsal |

Complementary

| | |
|-------------------|--------------------------|
| Colour code | GY |
| Material | PVC (polyvinyl chloride) |
| Stub stiffness | Flexible |
| Diameter | Internal: 18 mm |
| External diameter | 25 mm |

Environment

| | |
|---------------------------------------|----------------------------|
| Environmental characteristic | Conforming to AS/NZS 61386 |
| Ambient air temperature for operation | -15...60 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 25.0 cm |
| Package 1 Width | 52.0 cm |
| Package 1 Length | 52.0 cm |
| Package 1 Weight | 5.44 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

