

# Product data sheet

## Characteristics

# 9032TCM-GY

## conduit corrugated turbo pvc medium duty

### 32mm / 25m



### Main

Colour	Grey
Product brand	Clipsal

### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 23.6 mm
External diameter	32 mm

### Environment

Environmental characteristic	Conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

### Packing Units

Package 1 Weight	4.160 kg
Package 1 Height	162.000 mm
Package 1 width	338.000 mm
Package 1 Length	362.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>