

## Product data sheet

### Characteristics

# 9032THF-BK

## conduit rigid turbo ppblend hft heavy duty LSF0H(low smoke) 32mm / 4m

### Main

Colour	Black
Product brand	Clipsal

### Complementary

Colour code	BK
Material	PP (polypropylene)
Stub stiffness	Rigid
Diameter	Internal: 25.2 mm
External diameter	32 mm

### Environment

Environmental characteristic	Flame retardant Conforming to AS/NZS 61386
Ambient air temperature for operation	-5...120 °C

### Packing Units

Package 1 Weight	0.900 kg
Package 1 Height	32.000 mm
Package 1 width	32.000 mm
Package 1 Length	4000.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.