

Product data sheet

Characteristics

9050TCM10-GY

Conduit, Clipsal - Cable Management, Turbo PVC M/D 50mm/10m



Main

Colour	Grey
Product brand	Clipsal

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 39.4 mm
External diameter	50 mm

Environment

Environmental characteristic	Conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.5 cm
Package 1 Width	48.5 cm
Package 1 Length	54.0 cm
Package 1 Weight	2.54 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

