

Product data sheet

Characteristics

A15/15A-WE

SOCKET SWITCHED SINGLE A STYLE

STAINLESS STEEL



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	30 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	149.8 g
Package 1 Height	55 mm
Package 1 width	80 mm
Package 1 Length	122 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile