

## Product data sheet

### Characteristics

# A15NA-WE

## SOCKET SWITCHED SINGLE A STYLE

## STAINLESS STEEL



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Metal Plate

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Indicator light
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	30 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm




### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Package 1 Weight	0.168 kg
Package 1 Height	30.000 mm
Package 1 width	70.000 mm
Package 1 Length	115.000 mm

## Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>