

## Product data sheet

### Characteristics

# A15YA-WE

## SOCKET SWITCHED SINGLE A STYLE

## STAINLESS STEEL



### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	45 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	157.0 g
Package 1 Height	3 cm
Package 1 width	7 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	1.72 kg

Package 2 Height	10.6 cm
Package 2 width	18 cm
Package 2 Length	25.7 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	800.0 g
Package 3 Height	8.4 cm
Package 3 width	12.65 cm
Package 3 Length	17 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>