

Product data sheet

Characteristics

A15YA-WE

SOCKET SWITCHED SINGLE A STYLE

STAINLESS STEEL



Main

Colour	White electric
Product brand	Clipsal
Range of product	Metal Plate

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	45 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	157 g
Package 1 Height	3 cm
Package 1 width	7 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	800 g
Package 2 Height	8.4 cm
Package 2 width	12.65 cm
Package 2 Length	17 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Weight	1.72 kg
Package 3 Height	10.6 cm
Package 3 width	18 cm
Package 3 Length	25.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile