

## Product data sheet

### Characteristics

# A25A-WE

## Twin Switch Socket Outlet, 250V, 10A, A Style Deep Curved Plate



### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	13 cm
Package 1 Weight	0.192 kg
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	5
Package 2 Height	117 cm

Package 2 Width	102 cm
Package 2 Length	138 cm
Package 2 Weight	1.01 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	157 cm
Package 3 Width	305 cm
Package 3 Length	445 cm
Package 3 Weight	9.6 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>