

## Product data sheet

### Characteristics

# A9A15096

## contact OC - for iSW - 3A - 415V



### Main

Range of product	Acti 9
Device short name	IOF
Product or component type	OC contact
Signal contacts composition	1 C/O

### Complementary

[Ie] rated operational current	3 A at 415 V AC 6 A at 250 V AC
Mounting mode	Fixed
Mounting support	35 mm DIN rail
9 mm pitches	2
Height	77 mm
Width	18 mm
Depth	75 mm
Colour	White
Range compatibility	Acti 9 iSW
Auxiliary connection terminal	Screw terminal 10 mm <sup>2</sup>

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------