

Product data sheet

Characteristics

A9A26500

overvoltage release, Acti9, iMSU, voltage release, 230 V AC



Main

Range of product	Acti 9
Product or component type	Overvoltage release
Device short name	iMSU
[Uc] control circuit voltage	230 V AC 50/60 Hz
Threshold tripping voltage	255 V 275 V 3...15 s 300 V 1...5 s 350 V 0.25...0.75 s 400 V 0.07...0.2 s
9 mm pitches	2

Complementary

Range compatibility	Acti9 iC65 Acti 9 ARA Acti9 iDPN Vigi Acti9 iID Acti9 iSW-NA Acti 9 RCA Acti9 iDPN (China version) Acti9 iC60 double terminals miniature circuit breaker Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top and bottom: YES
Height	82.5 mm
Width	18 mm
Depth	68 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 0.5...4 mm ² - flexible Clamp terminal 1...6 mm ² - rigid
Wire stripping length	10 mm
Tightening torque	1 N.m
Compatibility code	IMSU

Environment

Standards	EN 50550
Quality labels	CE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	80.0 g
Package 1 Height	2.9 cm
Package 1 width	8.2 cm
Package 1 Length	9.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Weight	6.694 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	747.0 g
Package 3 Height	8.7 cm
Package 3 width	10 cm
Package 3 Length	26.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------