

## Product data sheet

### Characteristics

# A9A26907

Auxiliary contact, Acti9 A9A, iSD, 1 C/O, 100mA to 6A, 24VAC to 415VAC, 24VDC to 130VDC, bottom connection



### Main

Range of product	Acti9
Product or component type	Fault contact
Device short name	iSD
Signal contacts composition	1 C/O
[In] rated current	0.1...6 A at 24...240 V, AC 50/60 Hz 0.1...3 A at 415 V, AC 50/60 Hz 0.1...6 A at 24 V, DC 0.1...2 A at 48 V, DC 0.1...1.5 A at 60 V, DC 0.1...1 A at 130 V, DC
9 mm pitches	1

### Complementary

[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting location	Left side of circuit-breaker
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Height	86 mm
Width	9 mm
Depth	73 mm
Net weight	33 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) 1 cable(s) 1...4 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m bottom

### Environment

Standards	EN/IEC 60947-5-1 GB/T 14048.5
Product certifications	CE[RETURN]UKCA
Quality labels	EAC CCC CMIM
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	8.000 cm
Package 1 Length	9.300 cm
Package 1 Weight	40.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	569.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.380 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	<a href="#">End Of Life Information</a>