

Product data sheet

Characteristics

A9A27005

Acti 9 iC60, Rotary handle, for iC60, black handle



Main

Range of product	IID ISW 40...125 ISW-NA IC60
Product or component type	Rotary handle
Accessory / separate part type	Control accessories
Handle colour	Black
Rotary handle mounting style	Extended

Complementary

Mounting mode	Drawout Fixed
Rotary handle padlocking	Lockable in O position 3 padlocks max Padlock in OFF position
Rotary handle mounting location	Front Lateral

Environment

IP degree of protection	IP55
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	12.3 cm
Package 1 Length	47.0 cm
Package 1 Weight	670.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.872 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	45.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	47.488 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------