

Product data sheet

Characteristics

A9A27006

Rotary handle - for iC60 - red handle



Main

Range of product	ISW-NA IC60 IID ISW 40...125
Product or component type	Rotary handle
Accessory / separate part type	Control accessories
Handle colour	Red
Rotary handle mounting style	Extended

Complementary

Mounting mode	Drawout Fixed
Rotary handle padlocking	Padlock in OFF position 3 padlocks max Lockable in O position
Rotary handle mounting location	Lateral Front




Environment




IP degree of protection	IP55
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	12.5 cm
Package 1 Length	47.5 cm
Package 1 Weight	673.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.85 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------