



### Main

Range of product	Acti9
Device short name	iATLc+c
Product or component type	Multilevel centralized control auxiliary
[Uc] control circuit voltage	24...240 V AC 50/60 Hz impulse

### Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	2 entries for switch
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	86 mm
Width	18 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm <sup>2</sup> - rigid Tunnel type terminals 0.5...4 mm <sup>2</sup> - rigid - with cable end Tunnel type terminals 1...4 mm <sup>2</sup> - flexible Tunnel type terminals 1...4 mm <sup>2</sup> - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 Acti9 iTL iTLc Acti 9 Acti9 iTL iATLc Acti 9 Acti9 iTL iATLc+c

### Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	8 cm
Package 1 Length	9.5 cm
Package 1 Weight	75 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8.5 cm
Package 2 Width	10 cm
Package 2 Length	26.5 cm
Package 2 Weight	640 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.288 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------