

Product data sheet

Characteristics

A9C15413

Acti9, control by illuminated push-buttons iATLz



Main

Range of product	Acti9
Device short name	iATLz
Product or component type	Impedance adaptation auxiliary
[Uc] control circuit voltage	130...240 V AC 50/60 Hz

Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	Illuminated push-button 3 mA
Mounting mode	Fixed, on left side of TL
Mounting support	DIN rail
9 mm pitches	2
Height	86 mm
Width	18 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm ² - rigid Tunnel type terminals 0.5...4 mm ² - rigid - with cable end Tunnel type terminals 1...4 mm ² - flexible Tunnel type terminals 1...4 mm ² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs Acti 9 Acti9 iTL iTLc
Product compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	1.800 cm
Package 1 Length	9.000 cm
Package 1 Weight	94.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	9.200 cm
Package 2 Length	23.000 cm
Package 2 Weight	1.173 kg
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.458 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------