


## Product data sheet

### Characteristics

# A9N21038

Acti 9 - comb busbar - 3L+N balanced with Aux and Vigi - 9 mm pitch - 56 modules



### Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	56

### Complementary

Number of ways	22 ways Aux + N + L + Vigi
Poles configuration for 1 way	1 x 1P + N
Connection pitch	9 mm between phase and neutral
Connector type	Tooth
Distance between way	45 mm
Marking	N L1 N L2 N L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	112
Width	1000 mm
Colour	Light grey (RAL 7035)
Range compatibility	Acti 9 C40 Acti 9 DT40 Acti 9 DT40 Vigi Acti 9 iDPN Acti 9 DT60 Acti 9 DPN Vigi Multi 9 N40 Vigi

### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------